



# Locking Devices, Industrial, Duplex Receptacle, 15A 125V/10A 250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black

By Bryant  
Catalog # 7580DR



Locking Devices, Industrial, Duplex Receptacle, 10A 250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black RTP

## Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- Single point break-off tabs
- Mounting strap tabs lock the body and base together

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	7580DR
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	10A Duplex Receptacle Non-NEMA
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Duplex Receptacle
Type	Receptacle
UPC	781786002142

## Dimensions

Dimensions	3.28 in x 1.38 in x 1.41 in
Display Size	Standard Sized Product

Height	1.41 in
Length	3.28 in
Width	1.38 in

## Electrical Ratings

Amperage Rating	10 A
Connectivity	Terminal Screws
Current Rating	10 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY H-15 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 7580DR](#)