



Locking Devices, Industrial, Duplex Receptacle, 15A 125V/10A 250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # 7580DR



Locking Devices, Industrial, Duplex Receptacle, 10A 250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black RTP

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- Single point break-off tabs
- Mounting strap tabs lock the body and base together

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	7580DR
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	10A Duplex Receptacle Non-NEMA
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Duplex Receptacle
Type	Receptacle
UPC	781786002142

Dimensions

Dimensions	3.28 in x 1.38 in x 1.41 in
Display Size	Standard Sized Product

Height	1.41 in
Length	3.28 in
Width	1.38 in

Electrical Ratings

Amperage Rating	10 A
Connectivity	Terminal Screws
Current Rating	10 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY H-15 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 7580DR](#)