



Locking Devices, Industrial, Duplex Receptacle, 15A 125V/10A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # 7580GDR

Locking Devices, Industrial, Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black RTP



Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- Single point break-off tabs
- Mounting strap tabs lock the body and base together

General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	7580GDR
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Duplex Receptacle Non-NEMA
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Duplex Receptacle
Type	Receptacle
UPC	781786002166

Dimensions

Dimensions	3.28 in x 1.38 in x 1.41 in
Display Size	Standard Sized Product
Height	1.41 in
Length	3.28 in
Width	1.38 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY H-15 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-7580GDR-SPEC-EN | REV 6/2024