



Locking Devices, Industrial, Receptacle, 15A 125V/10A 250V, 3-Pole 3-Wire Non Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # 7582



Locking Devices, Industrial, Receptacle, 10A 250V, 3-Pole 3-Wire Non Grounding, Non-NEMA, Screw Terminal, Black

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	7582
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	10A Single Receptacle Non-NEMA
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Type	Receptacle
UPC	781786629493

Dimensions

Dimensions	3.28 in x 1.38 in x 1.41 in
Display Size	Standard Sized Product

Height	1.41 in
Length	3.28 in
Width	1.38 in

Electrical Ratings

Amperage Rating	10 A
Connectivity	Terminal Screws
Current Rating	10 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY Q-18 Catalog Page](#)
[Catalog Page - BRY H-15 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 7582](#)