



# Straight Blade Devices, Receptacles, Flush Mount Single, Industrial Grade, 4-Pole 4-Wire Non-Grounding, 60A 3-Phase 120/208V AC, 18-60R, Single Pack

By Bryant  
Catalog # 8360FR



Straight Blade Devices, Receptacles, Flush Mount Single,  
Industrial Grade, 4-Pole 4-Wire Non-Grounding, 60A 3-Phase  
120/208V AC, 18-60R, Black, Single Pack

## Application

Industrial Grade

## General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Smooth Face
Type	Single Receptacle
UPC	781786673403

## Dimensions

Dimensions	3.68 in x 2.25 in x 2.12 in
Display Size	Standard Sized Product
Height	2.12 in
Length	3.68 in
Weight	0.65 lb
Width	2.25 in

## Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Single Phase
Voltage Rating	Three Phase 120/208 VAC
Voltage Rating Description	3 Phase 120/208 VAC
Wattage	15000

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#6 AWG

## Certifications and Compliance

Nema Rating	18-60R
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant A-28 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Heavy Duty Straight Blade](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-8360FR-SPEC-EN | REV 7/2023