



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled, 4-Pole 4-Wire Non Grounding, 60A 3-Phase 120/208V AC, 18-60P

By Bryant
Catalog # 8362ANPB



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled, 4-Pole 4-Wire Non Grounding, 60A 3-Phase 120/208V AC, 18-60P, Black, Single Pack

General

Application	Heavy Duty
Catalog Number	8362ANPB
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Standard
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Industrial
Style	Heavy Duty
Type	Plug
UPC	781786673472

Dimensions

Dimensions	4.19 in x 3.25 in x 1.75 in
Display Size	Standard Sized
Height	1.75 in
Length	4.19 in
Weight	0.7 lb
Width	3.25 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Single Phase
Voltage Rating	Three Phase 120/208 VAC
Voltage Rating Description	3 Phase 120/208 VAC
Wattage	15000

Conductor Related

Cord Type	All Portable
Number Of Wires	4-Wire
Wire Size	#6 AWG to #4 AWG

Certifications And Compliance

Nema Rating	18-60P
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-28 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-8362ANPB-SPEC-EN | REV 6/2024