



Straight Blade Devices, Receptacles, Single, Hospital Grade, 20A 250V, 2-Pole 3-Wire Grounding, Back and Side Wired, 6-20R, Orange, Single Pack

By Bryant
Catalog # 8410IG



Straight Blade Devices, Receptacles, Single, Hospital Grade,
20A 250V, 2-Pole 3-Wire Grounding, Back and Side Wired, 6-
20R, Orange, Single Pack

Application

Hospital Grade

General

Color	Orange
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Hospital Grade
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786731431

Dimensions

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in
Length	3.28 in
Weight	0.15 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	5000

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	6-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-3 Catalog page](#)
[Catalog Page - Bryant B-2 Catalog page](#)
[Catalog Page - Bryant D-6 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-8410IG-SPEC-EN | REV 7/2023