



Straight Blade Devices, Receptacles, Flush Mount Single, Industrial Grade, 30A 3 Phase 250V AC, 3-Pole 4-Wire Grounding, 15-30R, Black, Single Pack

By Bryant
Catalog # 8430FR



Straight Blade Devices, Receptacles, Flush Mount Single, Industrial Grade, 30A 3 Phase 250V AC, 3-Pole 4-Wire Grounding, 15-30R, Black, Single Pack

General

Application	Industrial Grade
Catalog Number	8430FR
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Smooth Face
Type	Single Receptacle
UPC	781786673854

Dimensions

Dimensions	3.68 in x 2.25 in x 2.12 in
Display Size	Standard Sized Product
Height	2.12 in
Length	3.68 in
Weight	0.65 lb
Width	2.25 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	3750

Conductor Related

Number Of Wires	4-Wire
Wire Size	#10 AWG to #6 AWG

Certifications And Compliance

Nema Rating	15-30R
-------------	--------

Logistics

Carton Quantity	10
Pallet Quantity	1200

Product Assets

- [Catalog Page - BRY A-26 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Heavy Duty Straight Blade](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-8430FR-SPEC-EN | REV 6/2024