



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled, 3-Pole 4-Wire Grounding, 30A 3- Phase 250V AC, 15-30P, Single Pack

By Bryant
Catalog # [8432ANPB](#)



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled, 3-Pole 4-Wire Grounding, 30A 3- Phase 250V AC, 15-30P, Black, Single Pack

Application

Heavy Duty

General

Color	Black and White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Standard
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Industrial
Style	Heavy Duty
Type	Plug
UPC	781786673922

Dimensions

Display Size	Standard Sized
Length	4.19 in
Weight	0.75 lb
Width	3.25 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	7500

Conductor Related

Cord Type	All Portable
Number Of Wires	4-Wire
Wire Size	#12 AWG to #8 AWG

Certifications And Compliance

Nema Rating	15-30P
-------------	--------

Logistics

Carton Quantity	10
Pallet Quantity	1200

Product Assets

[Catalog Page - BRY A-26 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRY-8432ANPB-SPEC-EN | REV 5/2024