



Straight Blade Devices, Receptacles, Flush Mount Single, Industrial Grade, 50A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, 15- 50R, Black, Single Pack

By Bryant
Catalog # 8450FR



Straight Blade Devices, Receptacles, Flush Mount Single,
Industrial Grade, 50A 3-Phase 250V AC, 3-Pole 4-Wire
Grounding, 15-50R, Black, Single Pack

Features

- Flush Mount Single
- Industrial Grade
- 50A 3-Phase 250V AC
- 3-Pole 4-Wire Grounding
- 15-50R

Application

Industrial Grade

General

Catalog Number	8450FR
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
UPC	781786674103

Dimensions

Display Size	Standard Sized Product
Weight	0.65 lb

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Three Phase
Voltage Rating	250V kV
Voltage Rating Description	250V kV
Wattage	12500

Conductor Related

Number Of Wires	4-Wire Grounding
Wire Size	#10 AWG to #6 AWG

Certifications And Compliance

Nema Rating	15-50R
-------------	--------

Logistics

Carton Quantity	10
Pallet Quantity	1200

Product Assets

[Catalog Page - BRY A-27 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Heavy Duty Straight Blade Specifications - 8450FR](#)