



Straight Blade Devices, Receptacles, Flush Mount Single, Industrial Grade, 60A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, 15- 60R, Black, Single Pack

By Bryant
Catalog # 8460FR



Straight Blade Devices, Receptacles, Flush Mount Single,
Industrial Grade, 60A 3-Phase 250V AC, 3-Pole 4-Wire
Grounding, 15-60R, Black, Single Pack

Features

- Flush Mount Single
- Industrial Grade
- 60A 3-Phase 250V AC
- 3-Pole 4-Wire Grounding
- 15-60R

Application

Industrial Grade

General

Catalog Number	8460FR
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Smooth Face
Type	Single Receptacle
UPC	781786674257

Dimensions

Dimensions	3.68 in x 2.25 in x 2.12 in
Display Size	Standard Sized Product
Height	2.12 in
Length	3.68 in

Weight	0.6 lb
Width	2.25 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Three Phase
Voltage Rating	Three Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC
Wattage	12480

Conductor Related

Number Of Wires	4-Wire
Wire Size	#6 AWG

Certifications And Compliance

Nema Rating	15-60R
-------------	--------

Logistics

Carton Quantity	10
Pallet Quantity	1200

Product Assets

[Catalog Page - BRY A-28 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Heavy Duty Straight Blade Specifications - 8460FR](#)