



# Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled, 60A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, 15-60P, Single Pack

By Bryant  
Catalog # 8462ANPB



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled, 60A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, 15-60P, Black, Single Pack

## Application

Heavy Duty

## General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Standard
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Industrial
Style	Heavy Duty
Type	Plug
UPC	781786674325

## Dimensions

Dimensions	4.19 in x 3.25 in x 1.75 in
Display Size	Standard Sized
Height	1.75 in
Length	4.19 in
Weight	0.7 lb
Width	3.25 in

## Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Three Phase
Voltage Rating	Three Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC
Wattage	12480

## Conductor Related

Cord Type	All Portable
Number Of Wires	4-Wire
Wire Size	#6 AWG to #4 AWG

## Certifications and Compliance

Nema Rating	15-60P
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant A-28 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-8462ANPB-SPEC-EN | REV 7/2023