



## Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controller Accessories, Double Pole, 85A 600V AC, Side Wired Only

By Bryant  
Catalog # 85002D



Switches and Lighting Controls, Industrial Grade, Toggle  
Switches, Manual Motor Controller Accessories, Double Pole,  
85A 600V AC, Side Wired Only, Black

### General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Open Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2 Pole
OEM Brand Name	Hubbell Bryant
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Standard Toggle
Style	Motor Controller/Disconnect
Type	Back Wire
UPC	781786631922

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### Electrical Ratings

Amperage Rating	85 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	85 A
Current Rating	85 A
Phase	Single Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	51000

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Bryant E-12 Catalog page](#)  
[Catalog Page - Bryant G-6 Catalog page](#)  
[Catalog Page - Bryant G-2 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Motor Controllers and Disconnects](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-85002D-SPEC-EN | REV 7/2023