



Locking Devices, Flanged Receptacle, 20A 250V, 2- Pole 2-Wire Non-Grounding, Non-NEMA, Black

By Bryant
Catalog # 8809ER



Locking Devices, Flanged Receptacle, 20A 250V, 2-Pole 2-Wire Non-Grounding, NEMA L2-20 , White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	8809ER
Color	White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Flanged Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Type	Flanged Receptacle
UPC	781786630796

Dimensions

Dimensions	2.56 in x 2.56 in x 1.72 in
Display Size	Standard Sized Product
Height	1.72 in
Length	2.56 in
Width	2.56 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250V

Conductor Related

Number Of Wires	2-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L2-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY H-5 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-8809ER-SPEC-EN | REV 6/2024