



# Locking Devices, Locking Devices, Industrial, Male Plug, 20A 250V Pole, 2-Wire Non-Grounding, L2-20P, Screw Terminal, Gray

By Bryant  
Catalog # 9102N



Locking Devices, Industrial, Male Plug, 20A 250V Pole, 2-Pole 2-Wire, L2-20P, Screw Terminal, Black/White

## Application

Extra Heavy Duty Industrial

## General

Color	Black, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Type	Plugs
UPC	781786616837

## Dimensions

Dimensions	1.53 in x 1.53 in x 1.97 in
Display Size	Standard Sized
Height	1.97 in
Length	1.53 in
Width	1.53 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	2-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications and Compliance

Nema Rating	L2-20P
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-5 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[7101 - Locking Devices, Industrial, Female Connector Body, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20R, Screw Terminal, Gray](#)

[8809ER - Locking Devices, Flanged Receptacle, 20A 250V, 2-Pole 2-Wire Non-Grounding, Non-NEMA, Black](#)

[8808MB - Locking Devices, Flanged Inlet, 20A 250V, 2-Pole 2-Wire Non-Grounding, Non-NEMA, Black](#)

[7102N - Locking Devices, Industrial, Female Connector Body, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20R, Screw Terminal, Gray](#)

[7210B - Locking Devices, Industrial, Flush Receptacle, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20R, Screw Terminal, Gray](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-9102N-SPEC-EN | REV 7/2023