



Straight Blade Devices, Receptacles, Duplex, Decorator Hospital Grade, Isolated Ground, Back and Side Wired, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R

By Bryant
Catalog # 9200IGGRY



Straight Blade Devices, Receptacles, Duplex, Decorator Hospital Grade, Isolated Ground, Back and Side Wired, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray, Single Pack

Features

- Duplex
- Decorator Hospital Grade
- Isolated Ground
- Back and Side Wired
- 15A 125V

Application

Hospital Grade

General

Catalog Number	9200IGGRY
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Straight Blade
Style	Decorator
Type	Single Receptacle
UPC	781786741669

Dimensions

Dimensions	3.28 in x 1.36 in x 1.03 in
Display Size	Standard Sized Product
Height	1.03 in
Length	3.28 in

Weight	0.2 lb
Width	1.36 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-4](#) [Catalog Page](#)
[Catalog Page - BRY D-6](#) [Catalog Page](#)
[Catalog Page - BRY B-3](#) [Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Installation Manuals - WIRING_PD2504_INSTALLINST](#)
[Specifications - 9200IGGRY](#)

