



Straight Blade Devices, Receptacles, Duplex, Decorator Hospital Grade, Isolated Ground, 20A 125V, 2-Pole 3-Wire Grounding, Back and Side Wired, 5-20R

By Bryant
Catalog # 9300IGW



Straight Blade Devices, Receptacles, Duplex, Decorator Hospital Grade, Isolated Ground, 20A 125V, 2-Pole 3-Wire Grounding, Back and Side Wired, 5-20R, White, Single Pack

General

Application	Hospital Grade
Catalog Number	9300IGW
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Straight Blade
Style	Decorator
Type	Single Receptacle
UPC	781786741782

Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY B-3 Catalog Page](#)
- [Catalog Page - BRY A-4 Catalog Page](#)
- [Catalog Page - BRY D-6 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Installation Manuals - WIRING_PD2504_INSTALLINST](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-9300IGW-SPEC-EN | REV 6/2024