



Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Thermoset, Side Wired, 20A 250V

By Bryant
Catalog # 9326

Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Thermoset, Side Wired, 20A 250V, 3-Pole 3-Wire Non- Grounding, 10-20R, Black, Single Pack



Application

Industrial Grade

General

Color	Black
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786632462

Dimensions

Display Size	Standard Sized Product
Weight	0.1 lb

Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired Only
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	5000

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	10-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-23 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRY-9326-SPEC-EN | REV 5/2024