



**Straight Blade Devices,
Receptacles, Duplex, Decorator
Commercial/Industrial Grade, 20A
125V, 2-Pole 3-Wire Grounding, 5-
20R, Black, Single Pack**

By Bryant
Catalog # 9352BLK



Straight Blade Devices, Receptacles, Duplex, Decorator
Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire
Grounding, 5-20R, Black, Single Pack

General

Application	Specification Specification Grade
Catalog Number	9352BLK
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Decorator
Type	Duplex Receptacle
UPC	781786742147

Dimensions

Display Size	Standard Sized Product
Weight	0.25 lb

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY A-10 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Installation Manuals - WIRING_PD2504_INSTALLINST](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-9352BLK-SPEC-EN | REV 6/2024