



Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Reinforced Thermoplastic Polyester, 30A 125/250V, 14-30R

By Bryant
Catalog # 9430FR



Designed for plug-in EV charging applications, Hubbell's 14-50R receptacle is a premium and dependable solution to exceed the requirements of electric vehicle owners. This receptacle ensures a safe and efficient charging experience, providing peace of mind to EV users.

Application

Industrial Grade

General

Catalog Number	9430FR
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Smooth Face
Type	Single Receptacle
UPC	781786675933

Dimensions

Display Size	Standard Sized Product
Weight	0.6 lb

Electrical Ratings

Amperage Rating	30 A
-----------------	------

Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V
Wattage	7500

Conductor Related

Number Of Wires	4-Wire
Wire Size	#10 AWG to #6 AWG

Certifications And Compliance

Nema Rating	14-30R
-------------	--------

Logistics

Carton Quantity	10
Pallet Quantity	1200

Product Assets

[Catalog Page - BRY A-26 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Heavy Duty Straight Blade Literature - Electric Vehicle Charger Receptacle Specifications - 9430FR](#)