



# Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, 60A 125/250V, Reinforced Black Thermoplastic Polyester

By Bryant  
Catalog # 9460FR



Straight Blade Devices, Receptacles, Flush Mount Single,  
Commercial/Industrial Grade, 60A 125/250V, Reinforced Black  
Thermoplastic Polyester, 3-Pole 4-Wire Grounding, 14-60R,  
Black, Single Pack

## Application

Industrial Grade

## General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Smooth Face
Type	Single Receptacle
UPC	781786676480

## Dimensions

Display Size	Standard Sized Product
Weight	0.65 lb

## Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V
Wattage	15000

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#6 AWG

## Certifications and Compliance

Nema Rating	14-60R
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant A-28 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Heavy Duty Straight Blade](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-9460FR-SPEC-EN | REV 7/2023