



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled, 60A 125/250V, 3-Pole 4-Wire Grounding, 14-60P, Black, Single Pack

By Bryant
Catalog # 9462ANPB



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled, 60A 125/250V, 3-Pole 4-Wire Grounding, 14-60P, Black, Single Pack

Application

Heavy Duty

General

Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Standard
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Series	Industrial
Style	Heavy Duty
Type	Plug
UPC	781786676626

Dimensions

Display Size	Standard Sized
Weight	0.95 lb

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V
Wattage	15000

Conductor Related

Cord Type	All Portable
Number Of Wires	4-Wire
Wire Size	#6 AWG to #4 AWG

Certifications And Compliance

Nema Rating	14-60R
-------------	--------

Logistics

Carton Quantity	10
Pallet Quantity	1200

Product Assets

[Catalog Page - BRY A-28 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRY-9462ANPB-SPEC-EN | REV 5/2024