



Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Reinforced Thermoplastic Polyester, 30A 125V, 5-30R

By Bryant
Catalog # 9530FR



Straight Blade Devices, Receptacles, Flush Mount Single,
Commercial/Industrial Grade, Reinforced Thermoplastic
Polyester, 30A 125V, 2-Pole 3-Wire Grounding, 5-30R, Black,
Single Pack

Features

- Flush Mount Single
- Commercial/Industrial Grade
- Reinforced Thermoplastic Polyester
- 30A 125V
- 2-Pole 3-Wire Grounding

Application

Industrial Grade

General

| | |
|------------------------------|--|
| Catalog Number | 9530FR |
| Color | Black |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | Single |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| OEM Brand Name | Hubbell Bryant |
| Series | Heavy Duty |
| Style | Smooth Face |
| Type | Single Receptacle |
| UPC | 781786676732 |

Dimensions

| | |
|--------------|------------------------|
| Display Size | Standard Sized Product |
| Weight | 0.4 lb |

Electrical Ratings

| | |
|----------------------------|--------------------------|
| Amperage Rating | 30 A |
| Connectivity | Pressure Terminal Screws |
| Current / Amperage Rating | 30 A |
| Current Rating | 30 A |
| Phase | Single Phase |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |
| Wattage | 3750 |

Conductor Related

| | |
|-----------------|-------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #10 AWG to #6 AWG |

Certifications And Compliance

| | |
|-----------------------------|-------|
| Nema Rating | 5-30R |
| Standards - RoHS Compliance | CM |
| Status | |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 25 |
|-----------------|----|

Product Assets

[Catalog Page - BRY Q-18 Catalog Page](#)
[Catalog Page - BRY A-26 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Heavy Duty Straight Blade Specifications - 9530FR](#)