



Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Reinforced Thermoplastic Polyester, 30A 250V

By Bryant
Catalog # 9630IG



Straight Blade Devices, Receptacles, Flush Mount Single,
Commercial/Industrial Grade, Reinforced Thermoplastic
Polyester, 30A 250V, 2-Pole 3-Wire Grounding, 6-30R, Orange,
Single Pack, Isolated Ground

General

Application	Industrial Grade
Catalog Number	9630IG
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Straight Blade
Style	Extra Heavy Duty
Type	Single Receptacle
UPC	781786731080

Dimensions

Display Size	Standard Sized Product
Weight	0.35 lb

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	7500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#10 AWG to #6 AWG

Certifications And Compliance

Nema Rating	6-30R
-------------	-------

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalog Page - BRY A-26 Catalog Page](#)
- [Catalog Page - BRY D-6 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Heavy Duty Straight Blade](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-9630IG-SPEC-EN | REV 6/2024