



Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, 50A 250V, 2-Pole 3-Wire Grounding, 5-50R, Isolated Ground

By Bryant
Catalog # 9650IG



Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, 50A 250V, 2-Pole 3-Wire Grounding, 5-50R, Orange, Single Pack, Isolated Ground

Application

Industrial Grade

General

Color	Orange
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Straight Blade
Style	Extra Heavy Duty
Type	Single Receptacle
UPC	781786731097

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Single Phase
Voltage Rating	260 V
Voltage Rating Description	260 V
Wattage	12500

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#10 AWG to #6 AWG

Certifications and Compliance

Nema Rating	6-50R
-------------	-------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Literature - General Literature - Heavy Duty Straight Blade](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-9650IG-SPEC-EN | REV 7/2023