



Locking Devices, Locking Devices, Industrial, Male Plug, 20A 120/208V AC, 4-Pole 4-Wire Non Grounding, Non-NEMA, Screw Terminal, Yellow

By Bryant
Catalog # 9967NSY

Locking Devices, Industrial, Male Nylon Plug, 20A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non Grounding, Non-NEMA, Screw Terminal, Yellow



General

Application	Extra Heavy Duty Industrial
Catalog Number	9967NSY
Color	Sentinel Yellow
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Nylon Plug-For Replacement Use
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Type	Plugs
UPC	781786678835

Dimensions

Dimensions	2.11 in x 2.11 in x 2.60 in
Display Size	Standard Sized
Height	2.6 in
Length	2.11 in
Width	2.11 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Phase	Three Phase
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3 Phase Y 120/208 VAC
Wattage	

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY H-16 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-9967NSY-SPEC-EN | REV 6/2024