



Audio/Video Connector, D-Sub, Female 9- Pin, Screw Terminal, 10 Pack

By Bryant
Catalog # 9ST10



Audio/Video Connector, D-Sub, Female 9- Pin, Screw Terminal, 10 Pack

General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION VGA Analog Video Connections
Material - Mounting Hardware	Snap-On- Snap-Fit
Style	HD, 9-Pin
Temperature Rating	Per TIA
Type	Screw Term
UPC	662620289144

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Screw Terminals
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalog Page - Bryant R-17 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-9ST10-SPEC-EN | REV 7/2023