



Patch Cord, AV Plug and Play, 15-Pin Male to 8-Pin Male, 5'

By Bryant
Catalog # [AV15M05](#)

Patch Cord, AV Plug and Play, 15-Pin Male to 8-Pin Male, 5'



Application

X-End Plug-n-Play Patching Run

General

Boot Type	None
EU RoHS Indicator	Yes
Item Type	X-END AV Application Tails
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	Male to Male
Temperature Rating	Per TIA
Type	VGA, Plug-n-Play
UPC	662620220109

Dimensions

Outside Diameter	0.38
------------------	------

Electrical Ratings

Voltage Rating	600V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#28 AWG

Logistics

Carton Quantity	70
-----------------	----

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-AV15M05-SPEC-EN | REV 7/2023