



## Patch Cord, AV Plug and Play, 15-Pin Male to 8-Pin Male, 10'

By Bryant  
Catalog # [AV15M10](#)

Patch Cord, AV Plug and Play, 15-Pin Male to 8-Pin Male, 10'



### Application

X-End Plug-n-Play Patching Run

### General

Boot Type	None
EU RoHS Indicator	Yes
Item Type	X-END AV Application Tails
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	Male to Male
Temperature Rating	Per TIA
Type	VGA, Plug-n-Play
UPC	662620220116

### Dimensions

Outside Diameter	0.38
------------------	------

### Electrical Ratings

Voltage Rating	600V AC kV
----------------	------------

### Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#28 AWG

### Logistics

Carton Quantity	40
-----------------	----

### Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-AV15M10-SPEC-EN | REV 7/2023