



Temporary Lighting Products, 12/3 50' STW Light String, With Metal Guards, 5 Fixtures

By Bryant
Catalog # [BRY123S50MS](#)

Temporary Lighting Products, 12/3 50' STW Light String, With
Metal Guards, 5 Fixtures



General

Light Source	Incandescent
Series	Stringer Lights
Type	Straight Blade Light String, Metal Guard
UPC	781786380028

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 VAC

Product Assets

[Catalog Page - Bryant L-11 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Temporary Lighting Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY123S50MS-SPEC-EN | REV 7/2023