



## Temporary Lighting Products, 12/3 100' SJTW, Twist-Lock® Light String, With Plastic Guard, 10 Fixtures

By Bryant  
Catalog # [BRY123SJ100PT](#)

Temporary Lighting Products, 12/3 100' SJTW, Twist-Lock®  
Light String, With Plastic Guard, 10 Fixtures



### General

Light Source	Incandescent
Series	Stringer Lights
Type	Twist-Lock® Light String, Plastic Guard
UPC	781786379961

### Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	125 VAC

### Product Assets

[Catalog Page - Bryant L-11 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Temporary Lighting Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-BRY123SJ100PT-SPEC-EN | REV 7/2023