



Straight Blade Devices, Elastomeric, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, Screw Terminal, Black, Water/Dust- Tight Housing

By Bryant
Catalog # [BRY14W47BK](#)



Straight Blade Devices, Elastomeric, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, Screw Terminal, Black, Water/Dust-Tight Housing

General

Color	Black
Cord Range	0.325"-0.625"
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Straight
Type	Plug
UPC	781786378124

Dimensions

Length	3.16 in
Weight	0.3 lb
Width	1.85 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications and Compliance

Nema Rating	5-15P
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-22 Catalog page](#)
[Catalog Page - Bryant I-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[BRY60W47 - Straight Blade Devices, Watertight Series, Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Yellow](#)
[BRYWTCS1 - Watertight Replacement Cone Seal, Size 1](#)
[BRY14W47 - Straight Blade Devices, Elastomeric, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)
[BRY15W47BK - Straight Blade Devices, Elastomeric, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, Screw Terminal, Black, Water/Dust-Tight Housing](#)
[BRY15W47 - Straight Blade Devices, Elastomeric, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY14W47BK-SPEC-EN | REV 7/2023