



## Straight Blade Devices, Elastomeric, Male Plug Interior, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15P, Screw Terminal, Black, Water/Dust-Tight Housing

By Bryant  
Catalog # [BRY14W47IN](#)



Straight Blade Devices, Elastomeric, Male Plug Interior, 15A  
125V, 2-Pole 3-Wire Grounding, 5-15P, Screw Terminal, Black,  
Water/Dust-Tight Housing

### General

Color	White
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Type	Interiors
UPC	781786378131

### Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

### Conductor Related

Number Of Wires	3-Wire
-----------------	--------

### Certifications and Compliance

Nema Rating	5-15P
-------------	-------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Bryant I-8 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Watertight Wiring Devices](#)

### Related Products

[BRY60W47 - Straight Blade Devices, Watertight Series, Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Yellow](#)  
[BRYWTCS1 - Watertight Replacement Cone Seal, Size 1](#)  
[BRY14W47 - Straight Blade Devices, Elastomeric, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)  
[BRY14W47BK - Straight Blade Devices, Elastomeric, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, Screw Terminal, Black, Water/Dust-Tight Housing](#)  
[BRY50W50 - Watertight Series Replacement Caps, 15A, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-BRY14W47IN-SPEC-EN | REV 7/2023