



Straight Blade Devices, Elastomeric, Male Plug, 20A 250V, 2-Pole 3-Wire Grounding, 6-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant
Catalog # [BRY14W48](#)



Straight Blade Devices, Elastomeric, Male Plug, 20A 250V, 2-Pole 3-Wire Grounding, 6-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing

General

Color	Yellow
Cord Range	0.325"-0.625"
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Straight
Type	Plug
UPC	781786378162

Dimensions

Length	3.16 in
Weight	0.25 lb
Width	1.85 in

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications and Compliance

Nema Rating	6-20P
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-22 Catalog page](#)
[Catalog Page - Bryant I-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Watertight Wiring Devices](#)

Related Products

[BRY50W50BK - Watertight Series Replacement Caps, 15A, Black](#)
[BRY60W48D - Straight Blade Devices, Watertight Series, Receptacle, Duplex, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Yellow](#)
[BRYWTB1 - Watertight Replacement Bushing Set, Size 1](#)
[BRY60W48 - Straight Blade Devices, Watertight Series, Receptacle, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Yellow](#)
[BRY15W48 - Straight Blade Devices, Elastomeric, Female Connector Body, 20A 250V, 2-Pole 3-Wire Grounding, 6-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY14W48-SPEC-EN | REV 7/2023