



## Straight Blade Devices, Elastomeric, Male Plug, 15A 250V, 2-Pole 3-Wire Grounding, 6-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant  
Catalog # [BRY14W49](#)



Straight Blade Devices, Elastomeric, Male Plug, 15A 250V, 2-Pole 3-Wire Grounding, 6-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing

### General

Color	Yellow
Cord Range	0.325"-0.625"
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Straight
Type	Plug
UPC	781786378148

### Dimensions

Length	3.16 in
Weight	0.3 lb
Width	1.85 in

### Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	250 V
Voltage Rating Description	250 V

### Conductor Related

Number Of Wires	3-Wire
-----------------	--------

### Certifications and Compliance

Nema Rating	6-15P
-------------	-------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Bryant A-22 Catalog page](#)  
[Catalog Page - Bryant I-4 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Watertight Wiring Devices](#)

### Related Products

[BRY60W49 - Straight Blade Devices, Watertight Series, Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, 6-15R, Yellow](#)  
[BRY60W49D - Straight Blade Devices, Watertight Series, Receptacle, Duplex, 15A 250V, 2-Pole 3-Wire Grounding, 6-15R, Yellow](#)  
[BRY15W49 - Straight Blade Devices, Elastomeric, Female Connector Body, 15A 250V, 2-Pole 3-Wire Grounding, 6-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)  
[BRY50W50BK - Watertight Series Replacement Caps, 15A, Black](#)  
[BRYWTB1 - Watertight Replacement Bushing Set, Size 1](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-BRY14W49-SPEC-EN | REV 7/2023