



Straight Blade Devices, Elastomeric, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, Screw Terminal, Black, Water/Dust-Tight Housing



By Bryant
Catalog # [BRY15W47BK](#)

Straight Blade Devices, Elastomeric, Female Connector Body,
15A 125V, 2-Pole 3-Wire Grounding, 5-15P, Screw Terminal,
Black, Water/Dust-Tight Housing

General

Color	Black
Cord Range	0.325"-0.625"
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Straight
Type	Connector Body
UPC	781786378193

Dimensions

Length	4.42 in
Weight	0.3 lb
Width	1.85 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant I-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[BRYWTB1 - Watertight Replacement Bushing Set, Size 1](#)
[BRY60W47 - Straight Blade Devices, Watertight Series, Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Yellow](#)
[BRYWTCS1 - Watertight Replacement Cone Seal, Size 1](#)
[BRY14W47 - Straight Blade Devices, Elastomeric, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)
[BRY60W47D - Straight Blade Devices, Watertight Series, Receptacle, Duplex, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY15W47BK-SPEC-EN | REV 7/2023