



# Straight Blade Devices, Elastomeric, Female Connector Body Interior, 15A 125V, 5-15R, Screw Terminal, Water/Dust-Tight Housing

By Bryant  
Catalog # [BRY15W47IN](#)



Straight Blade Devices, Elastomeric, Female Connector Body Interior, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Screw Terminal, Black, Water/Dust-Tight Housing

## General

Color	White
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Type	Interiors
UPC	781786378209

## Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications and Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant I-8 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Watertight Wiring Devices](#)

## Related Products

[BRY60W47 - Straight Blade Devices, Watertight Series, Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Yellow](#)  
[BRYWTB1 - Watertight Replacement Bushing Set, Size 1](#)  
[BRY15W47 - Straight Blade Devices, Elastomeric, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)  
[BRY60W47D - Straight Blade Devices, Watertight Series, Receptacle, Duplex, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Yellow](#)  
[BRY15W47BK - Straight Blade Devices, Elastomeric, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, Screw Terminal, Black, Water/Dust-Tight Housing](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-BRY15W47IN-SPEC-EN | REV 7/2023