



# Straight Blade Devices, Elastomeric, Female Connector Body, 20A 250V, 2-Pole 3-Wire Grounding, 6-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing



By Bryant  
Catalog # [BRY15W48](#)

Straight Blade Devices, Elastomeric, Female Connector Body,  
20A 250V, 2-Pole 3-Wire Grounding, 6-20P, Screw Terminal,  
Yellow, Water/Dust-Tight Housing

## General

Color	Yellow
Cord Range	0.325"-0.625"
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Straight
Type	Connector Body
UPC	781786378230

## Dimensions

Length	4.42 in
Weight	0.3 lb
Width	1.85 in

## Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	250 V
Voltage Rating Description	250 V

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications and Compliance

Nema Rating	6-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant A-22 Catalog page](#)  
[Catalog Page - Bryant I-4 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Watertight Wiring Devices](#)

## Related Products

[BRY50W50BK - Watertight Series Replacement Caps, 15A, Black](#)  
[BRY15W49 - Straight Blade Devices, Elastomeric, Female Connector Body, 15A 250V, 2-Pole 3-Wire Grounding, 6-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)  
[BRYWTB1 - Watertight Replacement Bushing Set, Size 1](#)  
[BRY50W50 - Watertight Series Replacement Caps, 15A, Yellow](#)  
[BRY60W48 - Straight Blade Devices, Watertight Series, Receptacle, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-BRY15W48-SPEC-EN | REV 7/2023