



Straight Blade Devices, Elastomeric, Female Connector Body, 15A 250V, 2-Pole 3-Wire Grounding, 6-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing



By Bryant
Catalog # [BRY15W49](#)

Straight Blade Devices, Elastomeric, Female Connector Body,
15A 250V, 2-Pole 3-Wire Grounding, 6-15P, Screw Terminal,
Yellow, Water/Dust-Tight Housing

General

Color	Yellow
Cord Range	0.325"-0.625"
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Straight
Type	Connector Body
UPC	781786378216

Dimensions

Length	4.42 in
Weight	0.3 lb
Width	1.85 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications and Compliance

Nema Rating	6-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-22 Catalog page](#)
[Catalog Page - Bryant I-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Watertight Wiring Devices](#)

Related Products

[BRYWTB1 - Watertight Replacement Bushing Set, Size 1](#)
[BRY50W50BK - Watertight Series Replacement Caps, 15A, Black](#)
[BRY60W49 - Straight Blade Devices, Watertight Series, Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, 6-15R, Yellow](#)
[BRY15W48 - Straight Blade Devices, Elastomeric, Female Connector Body, 20A 250V, 2-Pole 3-Wire Grounding, 6-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)
[BRY50W50 - Watertight Series Replacement Caps, 15A, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY15W49-SPEC-EN | REV 7/2023