



Locking Devices, Male Plug, 15A 125V, 2-Pole 3- Wire Grounding, L5-15P, Screw Terminal, Black, Water/Dust-Tight Housing

By Bryant
Catalog # [BRY24W47BK](#)



Watertight Devices, Locking Devices, Male Plug, 15A 125V, 2-Pole 3- Wire Grounding, L5-15P, Screw Terminal, Black, Water/Dust-Tight Housing

Features

- Triple bypass seal keeps water away from electrical connections and works with previously installed devices
- Corrosion-resistant connection points
- High conductivity brass termination
- Cone seal accomodates any cable range
- Keyed interior for easy installation

General

Color	Black
Item Type	15A Watertight Plug
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none">• Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V• Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12• UV resistance:All exposed materials are UV stabilized• Flammability:UL94V2 (plugs, connectors, and interiors)
Type	Plugs
UPC	781786378285

Dimensions

Dimensions	1.85 in x 1.85 in x 3.21 in
Height	3.21 in
Length	1.85 in
Width	1.85 in

Electrical Ratings

Amperage Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#16/3 SJ to #10/3 SJ, #18/3 S to #12/3 S

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• IP69K• Listed to UL498• Certified to CSA C22.2 No. 42• Meets NEMA® WD-1, WD-6, and ANSI Standards• IP66 Suitability• NSF Certified (plugs, connectors and receptacles)
----------------------	---

Nema Rating	L5-15P
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY I-5 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.