



Locking Devices, Elastomeric, Female Connector Body, 15A277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant
Catalog # [BRY25W34](#)



Watertight Devices, Locking Devices, Elastomeric, Female Connector Body, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal, Yellow, Water/Dust-Tight Housing

Features

- Smooth body design minimizes collection points simplifying the wash down process
- Free-floating cap allows unwanted material to wash away during sanitation
- Unique cone seal prevents dirt and debris from collecting at the cable entrance
- PBT strain relief nut provides unparalleled impact resistance

General

Color	Yellow
Item Type	15A Watertight Connector
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none">• Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V• Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12• UV resistance:All exposed materials are UV stabilized• Flammability:UL94V2 (plugs, connectors, and interiors)
Type	Connector Body
UPC	781786378315

Dimensions

Dimensions	1.85 in x 1.85 in x 4.62 in
Height	4.62 in
Length	1.85 in
Width	1.85 in

Electrical Ratings

Amperage Rating	15 A
Voltage Rating	277 VAC
Voltage Rating Description	277 VAC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#16/3 SJ to #10/3 SJ, #18/3 S to #12/3 S

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• IP69K• Listed to UL498• Certified to CSA C22.2 No. 42• Meets NEMA® WD-1, WD-6, and ANSI Standards• IP66 Suitability• NSF Certified (plugs, connectors and receptacles)
Nema Rating	L7-15R

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - Bryant I-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Watertight Wiring Devices](#)

Related Products

[BRYWTB1 - Watertight Replacement Bushing Set, Size 1](#)
[BRY24W34 - Locking Devices, Male Plug, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)
[BRY50W50 - Watertight Series Replacement Caps, 15A, Yellow](#)
[BRYWTCS1 - Watertight Replacement Cone Seal, Size 1](#)
[BRY65W34D - Twist-Lock® Devices, Watertight Series, Receptacle, Duplex, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15R, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY25W34-SPEC-EN | REV 7/2023