



Straight Blade Devices, Female Connector Body, Elastomeric Water Tight, Industrial/Commercial Grade, Straight, 20A 125/250V, Non-NEMA

By Bryant
Catalog # [BRY26W08](#)



Watertight Devices, Locking Devices, Elastomeric, Male Plug, 3-Pole 3-Wire Non-Grounding, 20A 125/250V, Non-NEMA, Screw Terminal, Yellow, Water/Dust-Tight

Features

- Triple bypass seal keeps water away from electrical connections and works with previously installed devices
- Corrosion-resistant connection points
- High conductivity brass termination
- Cone seal accomodates any cable range
- Keyed interior for easy installation

General

Color	Yellow
Item Type	20A Watertight Plug
Number Of Poles	3-Pole
Type	Plugs
UPC	781786378360

Dimensions

Dimensions	2.51 in x 2.51 in x 3.96 in
Height	3.96 in
Length	2.51 in
Width	2.51 in

Electrical Ratings

Amperage Rating	20 A
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Number Of Wires	3-Wire
Wire Size	Min. cord: #16/3 SJ, #18/3 S, #18/4 SJ, #18/4 S, #18/5 S;Max. cord: #10/3 S, #10/4 S, #10/5 S

Certifications and Compliance

Industry Standard(s)	IP69K
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant I-6 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Watertight Wiring Devices](#)

Related Products

[BRY67W08 - Watertight Series, Locking Receptacle, 20A 125/250V AC, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Yellow](#)
[BRYWTCS2 - Watertight Replacement Cone Seal, Size 2](#)
[BRYWTB2 - Watertight Replacement Bushing Set, Size 2](#)
[BRY27W08 - Locking Devices, Elastomeric, Male Plug, 20A 125/250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY26W08-SPEC-EN | REV 7/2023