



# Locking Devices, Elastomeric, Male Plug, 20A 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-NEMA, Screw Terminal, Yellow, Water/Dust-Tight

By Bryant  
Catalog # [BRY26W09](#)



Watertight Devices, Locking Devices, Elastomeric, Male Plug, 20A 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-NEMA, Screw Terminal, Yellow, Water/Dust-Tight

## Features

- Triple bypass seal keeps water away from electrical connections and works with previously installed devices
- Corrosion-resistant connection points
- High conductivity brass termination
- Cone seal accomodates any cable range
- Keyed interior for easy installation

## General

Color	Yellow
Item Type	20A Watertight Plug
Number Of Poles	4-Pole
Type	Plugs
UPC	781786378377

## Dimensions

Dimensions	2.51 in x 2.51 in x 3.96 in
Height	3.96 in
Length	2.51 in
Width	2.51 in

## Electrical Ratings

Amperage Rating	20 A
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3 Phase Y 120/208 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	Min. cords: #12/3 SJ, #16/3 S, #14/4 SJ, #18/4 S, #18/5 S;Max. cord: #8/3 S, #8/4 S, #10/5 S

## Certifications And Compliance

Industry Standard(s)	IP69K
Nema Rating	Non-NEMA

## Logistics

Carton Quantity 10

## Product Assets

- [Catalog Page - BRY I-6 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Watertight Wiring Devices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-BRY26W09-SPEC-EN | REV 6/2024