



Locking Devices, Elastomeric, Male Plug, 20A 125V, 2-Pole 3-Wire Grounding, L5-20P, Screw Terminal, Black, Water/Dust-Tight Housing

By Bryant
Catalog # [BRY26W47BK](#)



Watertight Devices, Locking Devices, Elastomeric, Male Plug, 20A 125V, 2-Pole 3-Wire Grounding, L5-20P, Screw Terminal, Black, Water/Dust-Tight Housing

Features

- Triple bypass seal keeps water away from electrical connections and works with previously installed devices
- Corrosion-resistant connection points
- High conductivity brass termination
- Cone seal accomodates any cable range
- Keyed interior for easy installation

General

Color	Black
Item Type	20A Watertight Plug
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none"> • Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V • Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12 • UV resistance:All exposed materials are UV stabilized • Flammability:UL94V2 (plugs, connectors, and interiors)
Type	Plugs
UPC	781786378353

Dimensions

Dimensions	2.51 in x 2.51 in x 3.96 in
Height	3.96 in
Length	2.51 in
Width	2.51 in

Electrical Ratings

Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	Min. cord: #16/3 SJ, #18/3 S, #18/4 SJ, #18/4 S, #18/5 S;Max. cord: #10/3 S, #10/4 S, #10/5 S

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • IP69K • Listed to UL498 • Certified to CSA C22.2 No. 42 • Meets NEMA® WD-1, WD-6, and ANSI Standards • IP66 Suitability • NSF Certified (plugs, connectors and receptacles)
Nema Rating	L5-20P

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant I-6 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [BRYWTCS2 - Watertight Replacement Cone Seal, Size 2](#)
- [BRYWTB2 - Watertight Replacement Bushing Set, Size 2](#)
- [BRY67W47 - Watertight Series, Locking Receptacle, 20A 125V AC, 2-Pole 3-Wire Grounding, NEMA L5-20R, Yellow](#)
- [BRY27W47 - Locking Devices, Elastomeric, Female Connector Body, 20A 125V, 2-Pole 3-Wire Grounding, L5-20R, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)
- [BRY27W47BK - Locking Devices, Elastomeric, Female Connector Body, 20A 125V, 2-Pole 3-Wire Grounding, L5-20R, Screw Terminal, Black, Water/Dust-Tight Housing](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY26W47BK-SPEC-EN | REV 7/2023