



Locking Devices, Elastomeric, Male Plug, 20A125/250V, 3-Pole 4-Wire Grounding, L14-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant
Catalog # BRY26W74



Watertight Devices, Locking Devices, Elastomeric, Male Plug, 20A 125/250V, 3-Pole 4-Wire Grounding, L14-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing

Features

- Triple bypass seal keeps water away from electrical connections and works with previously installed devices
- Corrosion-resistant connection points
- High conductivity brass termination
- Cone seal accommodates any cable range
- Keyed interior for easy installation

Performance

- Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V
- Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12
- UV resistance:All exposed materials are UV stabilized
- Flammability:UL94V2 (plugs, connectors, and interiors)

General

Catalog Number	BRY26W74
Color	Yellow
Item Type	20A Watertight Plug
Number Of Poles	3-Pole
Type	Plugs
UPC	781786378407

Dimensions

Dimensions	2.51 in x 2.51 in x 3.96 in
Height	3.96 in
Length	2.51 in
Width	2.51 in

Electrical Ratings

Amperage Rating	20 A
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	Min. cord: #16/3 SJ, #18/3 S, #18/4 SJ, #18/4 S, #18/5 S;Max. cord: #10/3 S, #10/4 S, #10/5 S

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• IP69K• Listed to UL498• Certified to CSA C22.2 No. 42• Meets NEMA® WD-1, WD-6, and ANSI Standards• IP66 Suitability• NSF Certified (plugs, connectors and receptacles)
Nema Rating	L14-20P

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY I-6 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Watertight Wiring Devices Specifications - BRY26W74](#)