



Locking Devices, Elastomeric, Male Plug, 20A 3- Phase 250V AC, 3-Pole 4-Wire Grounding, L15-20P, Screw Terminal, Black, Water/Dust-Tight Housing

By Bryant
Catalog # [BRY26W75BK](#)

Watertight Devices, Locking Devices, Elastomeric, Male Plug, 20A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, L15-20P, Screw Terminal, Black, Water/Dust-Tight Housing

Features

- Triple bypass seal keeps water away from electrical connections and works with previously installed devices
- Corrosion-resistant connection points
- High conductivity brass termination
- Cone seal accomodates any cable range
- Keyed interior for easy installation

General

Color	Black
Item Type	20A Watertight Plug
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none">• Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V• Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12• UV resistance:All exposed materials are UV stabilized• Flammability:UL94V2 (plugs, connectors, and interiors)
Type	Plugs
UPC	781786378421

Dimensions

Dimensions	2.51 in x 2.51 in x 3.96 in
Height	3.96 in
Length	2.51 in
Width	2.51 in

Electrical Ratings

Amperage Rating	20 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC



Conductor Related

Number Of Wires	4-Wire
Wire Size	Min. cord: #16/3 SJ, #18/3 S, #18/4 SJ, #18/4 S, #18/5 S;Max. cord: #10/3 S, #10/4 S, #10/5 S

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• IP69K• Listed to UL498• Certified to CSA C22.2 No. 42• Meets NEMA® WD-1, WD-6, and ANSI Standards• IP66 Suitability• NSF Certified (plugs, connectors and receptacles)
Nema Rating	L15-20P

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant I-6 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[BRY27W75BK - Locking Devices, Elastomeric, Female Connector Body, 20A 3-Phase Delta 250V AC, L15-20R, Screw Terminal, Water/Dust-Tight Housing](#)
[BRY67W75 - Watertight Series, Locking Receptacle, 20A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, NEMA L15-20R, Yellow](#)
[BRY27W75 - Locking Devices, Elastomeric, Female Connector Body, 20A 3-Phase Delta 250V AC, L15-20R, Screw Terminal, Water/Dust-Tight Housing](#)
[BRYWTB2 - Watertight Replacement Bushing Set, Size 2](#)
[BRY26W75IN - Locking Devices, Elastomeric, Male Plug Interior, 20A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, L15-20P, Screw Terminal, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY26W75BK-SPEC-EN | REV 7/2023