



# Locking Devices, Elastomeric, Male Plug, 20A 125/250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant  
Catalog # [BRY27W08](#)



Watertight Devices, Locking Devices, Elastomeric, Female Connector Body, 20A 125/250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Yellow, Water/Dust-Tight Housing

## Features

- Smooth body design minimizes collection points simplifying the wash down process
- Free-floating cap allows unwanted material to wash away during sanitation
- Unique cone seal prevents dirt and debris from collecting at the cable entrance
- PBT strain relief nut provides unparalleled impact resistance

## General

Color	Yellow
Item Type	20A Watertight Connector
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"><li>• Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V</li><li>• Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12</li><li>• UV resistance:All exposed materials are UV stabilized</li><li>• Flammability:UL94V2 (plugs, connectors, and interiors)</li></ul>
Type	Connector Body
UPC	781786378544

## Dimensions

Dimensions	2.51 in x 2.51 in x 5.69 in
Height	5.69 in
Length	2.51 in
Width	2.51 in

## Electrical Ratings

Amperage Rating	20 A
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

## Conductor Related

Number Of Wires	3-Wire
Wire Size	Min. cord: #16/3 SJ, #18/3 S, #18/4 SJ, #18/4 S, #18/5 S;Max. cord: #10/3 S, #10/4 S, #10/5 S

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• IP69K</li><li>• Listed to UL498</li><li>• Certified to CSA C22.2 No. 42</li><li>• Meets NEMA® WD-1, WD-6, and ANSI Standards</li><li>• IP66 Suitability</li><li>• NSF Certified (plugs, connectors and receptacles)</li></ul>
----------------------	---

Nema Rating	Non-NEMA
-------------	----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant I-6 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Watertight Wiring Devices](#)

## Related Products

[BRY50W52 - Watertight Series Replacement Caps, 20A, Yellow](#)  
[BRYWTCS2 - Watertight Replacement Cone Seal, Size 2](#)  
[BRYWTB2 - Watertight Replacement Bushing Set, Size 2](#)  
[BRY26W08 - Straight Blade Devices, Female Connector Body, Elastomeric Water Tight, Industrial/Commercial Grade, Straight, 20A 125/250V, Non-NEMA](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-BRY27W08-SPEC-EN | REV 7/2023