



# Locking Devices, Elastomeric, Female Connector Body Interior, 20A 125V, 2-Pole 3-Wire Grounding, L5-20R, Screw Terminal, Black

By Bryant  
Catalog # [BRY27W47IN](#)



Watertight Devices, Locking Devices, Elastomeric, Receptacle Interior, 20A 125V, 2-Pole 3-Wire Grounding, L5-20R, Screw Terminal, Black

## General

Item Type	20A 125V Watertight Receptacle Replacement Interior
Number Of Poles	2-Pole
Type	Interiors
UPC	781786378520

## Electrical Ratings

Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications and Compliance

Nema Rating	L5-20R
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant I-8 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Watertight Wiring Devices](#)

## Related Products

[BRY67W47 - Watertight Series, Locking Receptacle, 20A 125V AC, 2-Pole 3-Wire Grounding, NEMA L5-20R, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-BRY27W47IN-SPEC-EN | REV 7/2023