



# Locking Devices, Elastomeric, Male Plug, 20A 125/250V, 3-Pole 4-Wire Grounding, L14-20R, Screw Terminal, Yellow Water/Dust Tight Housing

By Bryant  
Catalog # [BRY27W74](#)



Watertight Devices, Locking Devices, Elastomeric, Female Connector Body, 20A 125/250V, 3-Pole 4-Wire Grounding, L14-20R, Screw Terminal, Yellow, Water/Dust Tight Housing

## Features

- Smooth body design minimizes collection points simplifying the wash down process
- Free-floating cap allows unwanted material to wash away during sanitation
- Unique cone seal prevents dirt and debris from collecting at the cable entrance
- PBT strain relief nut provides unparalleled impact resistance

## General

Color	Yellow
Item Type	20A Watertight Connector
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> <li>• Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V</li> <li>• Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12</li> <li>• UV resistance:All exposed materials are UV stabilized</li> <li>• Flammability:UL94V2 (plugs, connectors, and interiors)</li> </ul>
Type	Connector Body
UPC	781786378582

## Dimensions

Dimensions	2.51 in x 2.51 in x 5.69 in
Height	5.69 in
Length	2.51 in
Width	2.51 in

## Electrical Ratings

Amperage Rating	20 A
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	Min. cord: #16/3 SJ, #18/3 S, #18/4 SJ, #18/4 S, #18/5 S;Max. cord: #10/3 S, #10/4 S, #10/5 S

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• IP69K</li> <li>• Listed to UL498</li> <li>• Certified to CSA C22.2 No. 42</li> <li>• Meets NEMA® WD-1, WD-6, and ANSI Standards</li> <li>• IP66 Suitability</li> <li>• NSF Certified (plugs, connectors and receptacles)</li> </ul>
Nema Rating	L14-20R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - Bryant I-6 Catalog page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Watertight Wiring Devices](#)

## Related Products

- [BRYWTB2 - Watertight Replacement Bushing Set, Size 2](#)
- [BRY26W74 - Locking Devices, Elastomeric, Male Plug, 20A125/250V, 3-Pole 4-Wire Grounding, L14-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)
- [BRY50W52 - Watertight Series Replacement Caps, 20A, Yellow](#)
- [BRYWTC52 - Watertight Replacement Cone Seal, Size 2](#)



A proud member of the Hubbell Family.

BRY-BRY27W74-SPEC-EN | REV 7/2023