



Locking Devices, Elastomeric, Female Connector Body Interior, 20A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16- 20R, Screw Terminal, Black

By Bryant
Catalog # [BRY27W76IN](#)



Watertight Devices, Locking Devices, Elastomeric, Receptacle Interior, 20A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16- 20R, Screw Terminal

General

Item Type	20A 480V Watertight Receptacle Replacement Interior
Number Of Poles	3-Pole
Type	Interiors
UPC	781786378636

Electrical Ratings

Amperage Rating	20 A
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480 VAC

Conductor Related

Number Of Wires	4-Wire
-----------------	--------

Certifications and Compliance

Nema Rating	L16-20R
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant I-8 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Watertight Wiring Devices](#)

Related Products

[BRY67W76 - Watertight Series, Locking Receptacle, 20A 3-Phase 480V AC, 3-Pole 4-Wire Grounding, NEMA L16-20R, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY27W76IN-SPEC-EN | REV 7/2023